

# Eaton S27G11S01A

Catalog Number: S27G11S01A

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 59A, 60 Hz, single-phase, 277 V, 120/240 V, 2 at -5% FCBN, 115 °C rise, 1 KVA, indoor-outdoor, 2B

## General specifications



Photo is representative

<a href="#">Product Name</a>	<a href="#">Catalog Number</a>
Eaton General purpose encapsulated transformer	S27G11S01A
	<a href="#">UPC</a>
	786685366098
<a href="#">Product Length/Depth</a>	<a href="#">Product Height</a>
5.75 in	11.28 in
<a href="#">Product Width</a>	<a href="#">Product Weight</a>
5.99 in	26 lb
<a href="#">Warranty</a>	<a href="#">Certifications</a>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	<a href="#">Catalog Notes</a>
	Model A

## Physical Attributes

### Coil material

Aluminum

### Design

EP

### Enclosure

NEMA 3R

### Frame

59A

### Tap size

2 at -5% FCBN

### Type

General-Purpose Encapsulated Transformer

### Wiring connection

2B

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Single-phase

### Primary voltage

277 V

### Secondary Voltage

120/240 V

### Temperature rise

115 °C rise

### Volt ampere rating

1 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - S27G11S01A](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)