

Eaton S27G12S03CU

Catalog Number: S27G12S03CU

Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 176, 60 Hz, single-phase, 277 V, 120 V, 2 at -5% FCBN, 115 °C rise, 3 KVA, indoor-outdoor, 2AB

General specifications



Photo is representative

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S27G12S03CU
	UPC
	786680083129
Product Length/Depth	Product Height
8 in	14.25 in
Product Width	Product Weight
7.69 in	65 lb
Warranty	Certifications

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Physical Attributes

Coil material

Copper

Design

EP

Enclosure

NEMA 3R

Frame

176

Tap size

2 at -5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

2AB

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

277 V

Secondary Voltage

120 V

Temperature rise

115 °C rise

Volt ampere rating

3 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S27G12S03CU](#)