

# Eaton S27N11E05CULS42

Catalog Number: S27N11E05CULS42

Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 177, 60 Hz, low sound 42 dB, single-phase, 277 V, 120/240 V, NONE, 115 °C rise, 5 KVA, indoor-outdoor, 513B



Photo is representative

## General specifications

<a href="#">Product Name</a>	<a href="#">Catalog Number</a>
Eaton General purpose encapsulated transformer	S27N11E05CULS42
	<a href="#">UPC</a>
	786685267234
<a href="#">Product Length/Depth</a>	<a href="#">Product Height</a>
9.89 in	16 in
<a href="#">Product Width</a>	<a href="#">Product Weight</a>
10.38 in	140 lb
<a href="#">Warranty</a>	<a href="#">Certifications</a>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	
	<a href="#">Catalog Notes</a>
	Low sound equal to 42 dB

## Physical Attributes

### Coil material

Copper

### Design

EP

### Enclosure

NEMA 3R

### Frame

177

### Tap size

None

### Type

General-Purpose Encapsulated Transformer

### Wiring connection

513B

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Single-phase

### Primary voltage

277 V

### Secondary Voltage

120/240 V

### Temperature rise

115 °C rise

### Volt ampere rating

5 kVA

## Miscellaneous

### Modification 1

Low sound 42 dB

### Special features

Electrostatically shielded

### Weathershield

Indoor-Outdoor

## Resources

### Catalogs

Eaton's Volume 2—Commercial Distribution

### Specifications and datasheets

Eaton Specification Sheet - S27N11E05CULS42



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)