

Eaton S27N11S16CULS42

Catalog Number: S27N11S16CULS42

Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 67, 60 Hz, low sound 42 dB, single-phase, 277 V, 120/240 V, NONE, 115 °C rise, 1.5 KVA, indoor-outdoor, 524A

General specifications



Photo is representative

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S27N11S16CULS42
	UPC
	786680080845
Product Length/Depth	Product Height
6.52 in	13.41 in
Product Width	Product Weight
6.37 in	0.001 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	Low sound equal to 42 dB

Physical Attributes

Coil material

Copper

Design

EP

Enclosure

NEMA 3R

Frame

67

Tap size

None

Type

General-Purpose Encapsulated Transformer

Wiring connection

524A

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

277 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

1.5 kVA

Miscellaneous

Modification 1

Low sound 42 dB

Weathershield

Indoor-Outdoor

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - S27N11S16CULS42



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)