

Eaton S27N11S76SS

Catalog Number: S27N11S76SS

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 58A, 60 Hz, single-phase, 277 V, 120/240 V, NONE, 115 °C rise, 0.75 KVA, indoor-outdoor, 524A

General specifications



Photo is representative

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S27N11S76SS
	UPC
	786680065125

Product Length/Depth	Product Height
5.75 in	11.28 in

Product Width	Product Weight
5.99 in	28 lb

Warranty	Certifications
--------------------------	--------------------------------

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

[Catalog Notes](#)

Grade 304 stainless steel enclosure

Physical Attributes

Coil material

Aluminum

Design

EP

Enclosure

NEMA 3R

Frame

58A

Tap size

None

Type

General-Purpose Encapsulated Transformer

Wiring connection

524A

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

277 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

0.75 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S27N11S76SS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)