

Eaton S29N11P16SS

Catalog Number: S29N11P16SS

Eaton General purpose encapsulated transformer, ep, NEMA 3R, Frame 67P, 60 Hz, single-phase, 208 V, 120/240 V, No Taps, 115 °C rise, 1.5



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S29N11P16SS
	UPC
	786680117312
Product Length/Depth	Product Height
0.001 in	0.001 in
Product Width	Product Weight
0.001 in	28 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	CSA Certified
	Catalog Notes
	304SS ENCLOSURE

Physical Attributes

Enclosure

NEMA 3R

Frame

Frame 67P

Tap size

No Taps

Type

EP

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

208 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

1.5

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S29N11P16SS](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)