

Eaton S29N11S10CULS47

Catalog Number: S29N11S10CULS47

Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 179, 60 Hz, low sound 47 dB, single-phase, 208 V, 120/240 V, NONE, 115 °C rise, 10 KVA, indoor-outdoor, 26A



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S29N11S10CULS47
	UPC
	786680051890
Product Length/Depth	Product Height
10.52 in	19 in
Product Width	Product Weight
13.38 in	192 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	
	Catalog Notes
	Low sound equal to 47 dB

Physical Attributes

Coil material

Copper

Design

EP

Enclosure

NEMA 3R

Frame

179

Tap size

None

Type

General-Purpose Encapsulated Transformer

Wiring connection

26A

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

208 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

10 kVA

Miscellaneous

Modification 1

Low sound 47 dB

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S29N11S10CULS47](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)