

Eaton S34N12P01P

Catalog Number: S34N12P01P

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 67P, 60 Hz, single-phase, 240/277 V, 120 V, NONE, 115 °C rise, 1 KVA, indoor-outdoor, 451B

General specifications



Photo is representative

| Product Name | Catalog Number |
|--|----------------|
| Eaton General purpose encapsulated transformer | S34N12P01P |
| | UPC |
| | 786680092442 |

| | |
|----------------------|----------------|
| Product Length/Depth | Product Height |
| 6.56 in | 13.03 in |

| | |
|---------------|----------------|
| Product Width | Product Weight |
| 5.53 in | 30 lb |

| Warranty | Certifications |
|--|----------------|
| Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. | |

Physical Attributes

Coil material

Aluminum

Design

EP

Enclosure

NEMA 3R

Frame

67P

Tap size

None

Type

General-Purpose Encapsulated Transformer

Wiring connection

451B

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

240/277 V

Secondary Voltage

120 V

Temperature rise

115 °C rise

Volt ampere rating

1 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S34N12P01P](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)