

Eaton S38G15E05XCU

Catalog Number: S38G15E05XCU

Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 178, 50-60 Hz, single-phase, 380 V, 115 V, 2 at -5% FCBN, 115 °C rise, 5 KVA, indoor-outdoor, 558D



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S38G15E05XCU
	UPC
	786680103919
Product Length/Depth	Product Height
9.89 in	16 in
Product Width	Product Weight
10.38 in	126 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	CSA Certified

Physical Attributes

Coil material

Copper

Design

EP

Enclosure

NEMA 3R

Frame

178

Tap size

2 at -5% FCBN

Type

General-purpose encapsulated transformer

Wiring connection

558D

Performance Ratings

Frequency rating

50-60 Hz

Phase

Single-phase

Primary voltage

380 V

Secondary Voltage

115 V

Temperature rise

115 °C rise

Volt ampere rating

5 kVA

Miscellaneous

Special features

Electrostatically shielded

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S38G15E05XCU](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)