

Eaton S38M11S05CU

Catalog Number: S38M11S05CU

Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 177, 60 Hz, single-phase, 380 V, 120/240 V, 2 at +2.5% FCAN, 4 at -2.5% FCBN, 115 °C rise, 5 KVA, indoor-outdoor, 83D



Photo is representative

General specifications

| | |
|--|-----------------------|
| Product Name | Catalog Number |
| Eaton General purpose encapsulated transformer | S38M11S05CU |
| | UPC |
| | 786680060557 |
| Product Length/Depth | Product Height |
| 9.89 in | 16 in |
| Product Width | Product Weight |
| 10.38 in | 124 lb |
| Warranty | Certifications |
| Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. | |

Physical Attributes

Coil material

Copper

Design

EP

Enclosure

NEMA 3R

Frame

177

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

83D

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

380 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

5 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S38M11S05CU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)