

# Eaton S39N12S10XSS

Catalog Number: S39N12S10XSS

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 180, 50-60 Hz, single-phase, 400 V, 120 V, NONE, 115 °C rise, 10 KVA, indoor-outdoor



Photo is representative

## General specifications

### Product Name

Eaton General purpose encapsulated transformer

### Catalog Number

S39N12S10XSS

### UPC

786680094194

### Product Length/Depth

10.52 in

### Product Height

19 in

### Product Width

13.38 in

### Product Weight

229 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

50/60 Hz, Grade 304 stainless steel enclosure

### Catalog Notes

50/60 Hz, Grade 304 stainless steel enclosure

## Physical Attributes

### Coil material

Aluminum

### Design

EP

### Enclosure

NEMA 3R

### Frame

180

### Tap size

None

### Type

General-Purpose Encapsulated Transformer

## Performance Ratings

### Frequency rating

50-60 Hz

### Phase

Single-phase

### Primary voltage

400 V

### Secondary Voltage

120 V

### Temperature rise

115 °C rise

### Volt ampere rating

10 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - S39N12S10XSS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)