

Eaton S40N14S02CEL24

Catalog Number: S40N14S02CEL24

Eaton, general purpose encapsulated transformer, ep, single-phase, pv: 190/200/208/220 x 380/400/416/440v, taps: none, sv: 110/220v, 115°C, 2 kva, indoor-outdoor, al windings, frame: 176

General specifications



Photo is representative

Product Name

Eaton General purpose encapsulated transformer

Catalog Number

S40N14S02CEL24

UPC

786680020360

Product Length/Depth

8 in

Product Height

14.25 in

Product Width

7.69 in

Product Weight

70 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Catalog Notes

CE Marked, With 24 inch leads

Physical Attributes

Coil material

Aluminum

Design

EP

Enclosure

NEMA 3R

Frame

176

Tap size

None

Type

General-Purpose Encapsulated Transformer

Wiring connection

538A

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

190 V, 200 V, 208 V, 220 V, 380 V, 400 V, 416 V, 440 V

Secondary Voltage

110/220 V

Temperature rise

115 °C rise

Volt ampere rating

2 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S40N14S02CEL24](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)