

Eaton S40N14S03N

Catalog Number: S40N14S03N

Eaton, general purpose encapsulated transformer, ep, single-phase, pv: 190/200/208/220 x 380/400/416/440v, taps: none, sv: 110/220v, 115°C, 3 kva, al windings, frame: 177, indoor-outdoor

General specifications



Photo is representative

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S40N14S03N
	UPC
	786680109393
Product Length/Depth	Product Height
9.89 in	16 in
Product Width	Product Weight
10.38 in	113 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	Model N

Physical Attributes

Coil material

Aluminum

Design

EP

Enclosure

NEMA 3R

Frame

177

Tap size

None

Type

General-Purpose Encapsulated Transformer

Wiring connection

538A

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

190 V, 200 V, 208 V, 220 V, 380 V, 400 V, 416 V, 440 V

Secondary Voltage

110/220 V

Temperature rise

115 °C rise

Volt ampere rating

3 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S40N14S03N](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)