

Eaton S40N14S05N

Catalog Number: S40N14S05N

Eaton, general purpose encapsulated transformer, ep, single-phase, pv: 190/200/208/220 x 380/400/416/440v, taps: none, sv: 110/220v, 115°C, 5 kva, al windings, frame: 178, indoor-outdoor



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S40N14S05N
	UPC
	786680109409
Product Length/Depth	Product Height
9.89 in	16 in
Product Width	Product Weight
10.38 in	137 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	Model N

Physical Attributes

Coil material

Aluminum

Design

EP

Enclosure

NEMA 3R

Frame

178

Tap size

None

Type

General-Purpose Encapsulated Transformer

Wiring connection

538A

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

190 V, 200 V, 208 V, 220 V, 380 V, 400 V, 416 V, 440 V

Secondary Voltage

110/220 V

Temperature rise

115 °C rise

Volt ampere rating

5 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S40N14S05N](#)