

# Eaton S42J11S25N

Catalog Number: S42J11S25N

Eaton General purpose encapsulated transformer medium voltage, EP, Single-phase, PV: 2400V, Taps: 4 at -2.5% FCBN, SV: 120/240V, 115°C, 25 kVA, Al windings, Frame: 190, Indoor-Outdoor



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose encapsulated transformer medium voltage	S42J11S25N
	<b>UPC</b>
	786680101380
<b>Product Length/Depth</b>	<b>Product Height</b>
14 in	26 in
<b>Product Width</b>	<b>Product Weight</b>
16 in	405 lb
<b>Warranty</b>	<b>Catalog Notes</b>
Eaton Selling Policy 25-000, one (1) year Model N from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

## defaultTaxonomyAttributeLabel

### Type

General-Purpose Encapsulated Transformer

### Coil material

Aluminum

### Frequency rating

60 Hz

### Phase

Single-phase

### Primary voltage

2,400 V

### Secondary Voltage

120/240 V

### Temperature rise

115 °C rise

### Design

EP

### Enclosure

NEMA 3R

### Frame

190

### Tap size

4 at -2.5% FCBN

### Volt ampere rating

25 kVA

### Weathershield

Indoor-Outdoor

### Wiring connection

12A

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Multimedia

[Eaton's Transformer Flex Center](#)

### Specifications and datasheets

[Eaton Specification Sheet - S42J11S25N](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)