

Eaton S42N11S16N

Catalog Number: S42N11S16N

General-Purpose Encapsulated TX, EP, Single-phase, PV: 2400V, Taps: None, SV: 120/240V, 115°C, 1.5 kVA, Al windings, Frame: 68, Indoor-Outdoor

General specifications



Photo is representative

Product Name	Catalog Number
Eaton General purpose encapsulated transformer medium voltage	S42N11S16N
	UPC
	786680101212

Product Length/Depth	Product Height
6.52 in	13.41 in

Product Width	Product Weight
6.37 in	38 lb

Warranty	Catalog Notes
Eaton Selling Policy 25-000, one (1) year Model N from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

defaultTaxonomyAttributeLabel

Special features

AI WINDINGS

Type

General-Purpose Encapsulated Transformer

Coil material

Aluminum

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

2,400 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Design

EP

Enclosure

NEMA 3R

Frame

68

Tap size

None

Volt ampere rating

1.5 kVA

Weathershield

INDOOR-OUTDOOR

Wiring connection

524D

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Multimedia

[Eaton's Transformer Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - S42N11S16N](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)