

Eaton S42-SP

Catalog Number: S42-SP

Eaton Arrow Hart heavy-duty universal nema power plug , #10-6 AWG, 30A/50A, Commercial|range & dryer, 250V, Back wire, Black, Brass, PVC, 6-30P, 6-50P, Screw, 1.10", PVC, Retail Box

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Arrow Hart heavy-duty universal NEMA power plug	S42-SP
	UPC
	032664517846
Product Length/Depth	Product Height
1.38 in	3.37 in
Product Width	Product Weight
2.87 in	0.455 lb
Certifications	
UL Listed	

defaultTaxonomyAttributeLabel

Device type

Plug

Special features

Non-grounding

Type

Angled plug

Amperage Rating

30 A/50 A

Voltage rating

250V

Contact material

Brass

Features

Non-grounding

Application

Commercial, range and dryer

Device grade

Heavy-duty industrial specification grade

Wiring method

Back wire

Number of wires

3

Number Of Poles

Three-pole

Style type

Power, Universal angled body

Cord range

1.10"

Material

PVC

Packaging type

Retail Box

Color

Black

Connection type

Resources

Brochures

[Flush mount receptacles sell sheet](#)

Catalogs

[Arrow Hart Buyers Guide Section B](#)

Specifications and datasheets

[Eaton Specification Sheet - S42-SP](#)

Screw

Allowable wire size

#10-6 AWG

NEMA configuration

6-30P, 6-50P

Torque rating

20 lbf-inch

Design type

Angled straight blade

Face/body material

PVC



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia