

Eaton S44M14S25

Catalog Number: S44M14S25

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 182, 60 Hz, single-phase, 440 V, 110/220 V, 2 at +2.5% FCAN, 4 at -2.5% FCBN, 115 °C rise, 25 KVA, indoor-outdoor, 83G



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S44M14S25
	UPC
	786680080869
Product Length/Depth	Product Height
14.12 in	23.31 in
Product Width	Product Weight
16.35 in	0.001 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Aluminum

Design

EP

Enclosure

NEMA 3R

Frame

182

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

83G

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

440 V

Secondary Voltage

110/220 V

Temperature rise

115 °C rise

Volt ampere rating

25 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S44M14S25](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)