

Eaton S48D11B10SSCU

Catalog Number: S48D11B10SSCU

Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 180, 60 Hz, single-phase, 480 V, 120/240 V, 2 at +2.5% FCAN, 2 at -2.5% FCBN, 80 °C rise, 10 KVA, indoor-outdoor, 16A



Photo is representative

General specifications

Product Name

Eaton General purpose encapsulated transformer

Catalog Number

S48D11B10SSCU

UPC

786680103988

Product Length/Depth

10.52 in

Product Height

19 in

Product Width

13.38 in

Product Weight

250 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

CSA Certified

Catalog Notes

Grade 304 Stainless Steel Enclosure

Physical Attributes

Coil material

Copper

Design

EP

Enclosure

NEMA 3R

Frame

180

Tap size

2 at +2.5% FCAN, 2 at -2.5% FCBN

Type

General-purpose encapsulated transformer

Wiring connection

16A

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

480 V

Secondary Voltage

120/240 V

Temperature rise

80 °C rise

Volt ampere rating

10 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S48D11B10SSCU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)