

# Eaton S48D11E01CU

Catalog Number: S48D11E01CU

Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 59A, 60 Hz, single-phase, 480 V, 120/240 V, 2 at +2.5% FCAN, 2 at -2.5% FCBN, 115 °C rise, 1 KVA, indoor-outdoor, 539A

## General specifications



Photo is representative

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S48D11E01CU
	UPC
	786680075339
Product Length/Depth	Product Height
5.75 in	11.28 in
Product Width	Product Weight
5.99 in	28 lb
Warranty	Certifications

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

## Physical Attributes

### Coil material

Copper

### Design

EP

### Enclosure

NEMA 3R

### Frame

59A

### Tap size

2 at +2.5% FCAN, 2 at -2.5% FCBN

### Type

General-Purpose Encapsulated Transformer

### Wiring connection

539A

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Single-phase

### Primary voltage

480 V

### Secondary Voltage

120/240 V

### Temperature rise

115 °C rise

### Volt ampere rating

1 kVA

## Miscellaneous

### Special features

Electrostatically shielded

### Weathershield

Indoor-Outdoor

## Resources

### Catalogs

Eaton's Volume 2—Commercial Distribution

### Specifications and datasheets

Eaton Specification Sheet - S48D11E01CU



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)