

Eaton S48D11S05CUS6

Catalog Number: S48D11S05CUS6

Eaton, general purpose encapsulated transformer, ep single-phase 480v 2 at +2.5% fcan 2 at -2.5% fcbn 120/240v 115°c 5 kva copper windings 177 16a indoor-outdoor 60 hz.



Photo is representative

General specifications

Product Name

Eaton General purpose encapsulated transformer

Catalog Number

S48D11S05CUS6

UPC

786680112362

Product Length/Depth

9.89 in

Product Height

16 in

Product Width

10.38 in

Product Weight

124 lb

Warranty

Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Catalog Notes

Grade 316 stainless steel enclosure (does not imply NEMA 4X rating).



Powering Business Worldwide

Physical Attributes

Coil material

Copper

Design

EP

Frame

177

Tap size

2 at +2.5% FCAN 2 at -2.5% FCBN

Type

General-purpose encapsulated transformer

Wiring connection

16A

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

5 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S48D11S05CUS6](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)