

Eaton S48G11E15CUS6

Catalog Number: S48G11E15CUS6

Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 180, 60 Hz, single-phase, 480 V, 120/240 V, 2 at -5% FCBN, 115 °C rise, 15 KVA, indoor-outdoor, 10A



Photo is representative

General specifications

Product Name

Eaton General purpose encapsulated transformer

Catalog Number

S48G11E15CUS6

UPC

786680097539

Product Length/Depth

10.52 in

Product Height

19 in

Product Width

13.38 in

Product Weight

228 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Catalog Notes

Grade 316 stainless steel enclosure

Physical Attributes

Coil material

Copper

Design

EP

Enclosure

NEMA 3R

Frame

180

Tap size

2 at -5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

10A

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

15 kVA

Miscellaneous

Special features

Electrostatically shielded

Weathershield

Indoor-Outdoor

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - S48G11E15CUS6



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)