

Eaton S48G11P16P

Catalog Number: S48G11P16P

Eaton General purpose encapsulated transformer, EP, copper, 67P, 60 Hz, single-phase, 480 V, 120/240 V, 2 at -5% FCBN, 115 °C rise, 1.5 KVA, indoor-outdoor, 2D



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S48G11P16P
	UPC
	786680112485
Product Length/Depth	Product Height
0.001 in	0.001 in
Product Width	Product Weight
0.001 in	32 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Copper

Design

EP

Frame

67P

Tap size

2 at -5% FCBN

Type

General-purpose encapsulated transformer

Wiring connection

2D

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

1.5 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S48G11P16P](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)