

Eaton S48G11S02N

Catalog Number: S48G11S02N

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 68, 60 Hz, single-phase, 480 V, 120/240 V, 2 at -5% FCBN, 115 °C rise, 2 KVA, indoor-outdoor, 2D

General specifications



Photo is representative

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S48G11S02N
	UPC
	786680101816
Product Length/Depth	Product Height
6.52 in	13.41 in
Product Width	Product Weight
6.37 in	46 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	Model N

Physical Attributes

Coil material

Aluminum

Design

EP

Enclosure

NEMA 3R

Frame

68

Tap size

2 at -5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

2D

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

2 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S48G11S02N](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)