

Eaton S48G11S25LS47

Catalog Number: S48G11S25LS47

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 300A, 60 Hz, low sound 47 dB, single-phase, 480 V, 120/240 V, 2 at -5% FCBN, 115 °C rise, 25 KVA, indoor-outdoor, S452V



Photo is representative

General specifications

Product Name

Eaton General purpose encapsulated transformer

Catalog Number

S48G11S25LS47

UPC

786680088117

Product Length/Depth

14.06 in

Product Height

28.24 in

Product Width

22.42 in

Product Weight

712 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Catalog Notes

Low sound equal to 47 dB

Physical Attributes

Coil material

Aluminum

Design

EP

Enclosure

NEMA 3R

Frame

300A

Tap size

2 at -5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

S452V

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

25 kVA

Miscellaneous

Modification 1

Low sound 47 dB

Weathershield

Indoor-Outdoor

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - S48G11S25LS47

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)