

# Eaton S60N11B26

Catalog Number: S60N11B26

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 56, 60 Hz, single-phase, 600 V, 120/240 V, NONE, 80 °C rise, 0.25 KVA, indoor-outdoor, 524B

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose encapsulated transformer	S60N11B26
	<b>UPC</b>
	786680060458

<b>Product Length/Depth</b>	<b>Product Height</b>
4.06 in	8.97 in

<b>Product Width</b>	<b>Product Weight</b>
4.87 in	11.5 lb

<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

## Physical Attributes

### Coil material

Aluminum

### Design

EP

### Enclosure

NEMA 3R

### Frame

56

### Tap size

None

### Type

General-Purpose Encapsulated Transformer

### Wiring connection

524B

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Single-phase

### Primary voltage

600 V

### Secondary Voltage

120/240 V

### Temperature rise

80 °C rise

### Volt ampere rating

0.25 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - S60N11B26](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)