

Eaton S84N11E25XCE

Catalog Number: S84N11E25XCE

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 50-60 Hz, single-phase, 380 V, 400 V, 415 V, 440 V, 460 V, 480 V, 120/240 V, NONE, 115 °C rise, 25 KVA, indoor-outdoor



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S84N11E25XCE
	UPC
	786680049606
Product Length/Depth	Product Height
0.001 in	0.001 in
Product Width	Product Weight
0.001 in	0.001 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	50/60 Hz, CE Marked

Physical Attributes

Coil material

Aluminum

Design

EP

Enclosure

NEMA 3R

Tap size

None

Type

General-Purpose Encapsulated Transformer

Performance Ratings

Frequency rating

50-60 Hz

Phase

Single-phase

Primary voltage

380 V, 400 V, 415 V, 440 V, 460 V, 480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

25 kVA

Miscellaneous

Special features

Electrostatically shielded

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S84N11E25XCE](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)