

Eaton SDC15-LA

Catalog Number: SDC15-LA

Eaton dimmer and fan speed control, No neutral required, #14 -12 AWG, Flush, 120 Vac, Back and side, Maintained, Light almond, 60 Hz, Incandescent, MLV, ELV, Fan, Halogen, Single-pole, Single pole, Single-phase, Polycarbonate, 300W 663239



General specifications

| | |
|------------------------------------|----------------------|
| Product Name | Catalog Number |
| Eaton dimmer and fan speed control | SDC15-LA |
| UPC | Product Length/Depth |
| 032664663239 | 2 in |
| Product Height | Product Width |
| 4.25 in | 2 in |
| Product Weight | Certifications |
| 0.28 lb | cULus Listed NOM |

Electrical Ratings

Frequency rating

60 Hz

Load type

ELV

INC

Fan

HAL

MLV

Number Of Poles

Single-pole

Number of ways

Single-way

Phase

Single-phase

Torque rating

14 lbf-inch

Voltage rating

120 V

Installation Specifications

Mounting method

Flush

Wiring method

Back and side

Material Specifications

Color

Light almond

Material

Polycarbonate

Product Specifications

Connection type

Side

Back

Resources

Specifications and datasheets

[Eaton Specification Sheet - SDC15-LA](#)

[Slide dimmers and fan controls spec sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)