

# Eaton SDC15-V

Catalog Number: SDC15-V

Eaton dimmer and fan speed control, No neutral required, #14 -12 AWG, Flush, 120 Vac, Back and side, Maintained, Ivory, 60 Hz, Incandescent, MLV, ELV, Fan, Halogen, Single-pole, Single pole, Single-phase, Polycarbonate, 300W 663246



## General specifications

Product Name	Catalog Number
Eaton dimmer and fan speed control	SDC15-V
UPC	Product Length/Depth
032664663246	2.05 in
Product Height	Product Width
4.31 in	2.08 in
Product Weight	Certifications
0.28 lb	cULus Listed NOM

## Electrical Ratings

### Frequency rating

60 Hz

### Load type

Fan  
MLV  
HAL  
INC  
ELV

### Number Of Poles

Single-pole

### Number of ways

Single-way

### Phase

Single-phase

### Torque rating

14 lbf-inch

### Voltage rating

120 V

## Installation Specifications

### Mounting method

Flush

### Wiring method

Back and side

## Material Specifications

### Color

Ivory

### Material

Polycarbonate

## Product Specifications

### Connection type

Side  
Back

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - SDC15-V](#)

[Slide dimmers and fan controls spec sheet](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)