

Eaton SDC15-W

Catalog Number: SDC15-W

Eaton dimmer and fan speed control, No neutral required, #14 -12 AWG, Flush, 120 Vac, Back and side, Maintained, White, 60 Hz, Incandescent, MLV, ELV, Fan, Halogen, Single-pole, Single pole, Single-phase, Polycarbonate, 300W 663253



General specifications

Product Name	Catalog Number
Eaton dimmer and fan speed control	SDC15-W
UPC	Product Length/Depth
032664663253	2.05 in
Product Height	Product Width
4.31 in	2.07 in
Product Weight	Certifications
0.285 lb	cULus Listed NOM

Electrical Ratings

Frequency rating

60 Hz

Load type

INC

Fan

MLV

HAL

ELV

Number Of Poles

Single-pole

Number of ways

Single-way

Phase

Single-phase

Torque rating

14 lbf-inch

Voltage rating

120 V

Installation Specifications

Mounting method

Flush

Wiring method

Back and side

Material Specifications

Color

White

Material

Polycarbonate

Product Specifications

Connection type

Back

Side

Resources

Specifications and datasheets

[Eaton Specification Sheet - SDC15-W](#)

[Slide dimmers and fan controls spec sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)