

Eaton SDR 50

Catalog Number: SDR 50

Eaton Crouse-Hinds series Cable-Gard SDR static discharge reel, 100A, 50 ft, Steel, Weathertight, Single 7x30

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Cable-Gard SDR static discharge reel	SDR 50
	UPC
	782274689685
Product Length/Depth	Product Height
13.75 in	16.25 in
Product Width	Product Weight
6.12 in	12 lb

Photo is representative

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

3

3R

Product specifications

Application

Lift

Wire size

#16 AWG

Number of conductors

3

Cable length

20 ft

Amperage Rating

100A

Voltage rating

600 Vac

Material

Steel

Special features

Weathertight

Type

Single 7 x 30

Resources

Catalogs

[SDR Static Discharge Reels and W Series Cable Reels catalog page](#)

Installation instructions

[IF 1265 - Static Discharge Reels](#)

Specifications and datasheets

[Eaton Specification Sheet - SDR 50](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)