

Eaton SF10P-W

Catalog Number: SF10P-W

Eaton 0-10V dimmer, No neutral required, #14 – 12 AWG, Flush, 120/277 Vac, Back and side, Wire Leads, Maintained, White, 60Hz, LED, Fluorescent, Single-pole, Three-way, Single-phase, Polycarbonate, 1200/1660W 736926



General specifications

Product Name	Catalog Number
Eaton slide dimmer	SF10P-W
UPC	Product Length/Depth
032664736926	2 in
Product Height	Product Width
4.3 in	2 in
Product Weight	Certifications
0.233 lb	cULus Listed NOM

defaultTaxonomyAttributeLabel

Frequency rating

60 Hz

Special features

No neutral required

Voltage rating

120/277 V

Number Of Poles

Single-pole, Three-way

Phase

Single-phase

Power consumption

1200 W

1660 W

Wiring method

Back and side, wire leads

Mounting method

Flush

Closure type

Maintained

Load type

FLR

LED

Material

Polycarbonate

Number of ways

Three-way

Torque rating

14 lbf-inch

Color

White

Connection type

Back

Wire

Side

Resources

Installation videos

[How to install Eaton's universal slide dimmers](#)

Specifications and datasheets

[Eaton Specification Sheet - SF10P-W](#)

[Slide 0-10V dimmers spec sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)