

# Eaton SI10P-BK

Catalog Number: SI10P-BK

Eaton slide dimmer, No neutral required, #14 -12 AWG, Flush, 120 Vac, Back and side, Maintained, Black, 60 Hz, Incandescent, halogen, MLV, Single-pole, Three-way, Single-phase, Polycarbonate, 1000W 713217



## General specifications

Product Name	Catalog Number
Eaton slide dimmer	SI10P-BK
UPC	Product Length/Depth
032664713217	3 in
Product Height	Product Width
4.25 in	2 in
Product Weight	Certifications
0.28 lb	cULus Listed NOM

## defaultTaxonomyAttributeLabel

### Frequency rating

60 Hz

### Special features

No neutral required

### Voltage rating

120 V

### Number Of Poles

Single-pole, Three-way

### Phase

Single-phase

### Power consumption

1000 W

### Wiring method

Back and side

### Mounting method

Flush

### Closure type

Maintained

### Load type

INC

HAL

MLV

### Material

Polycarbonate

### Number of ways

Three-way

### Torque rating

14 lbf-inch

### Color

Black

### Connection type

Back

Side

## Resources

### Installation videos

[How to install Eaton's universal slide dimmers](#)

### Specifications and datasheets

[Eaton Specification Sheet - SI10P-BK](#)

[Slide dimmers and fan controls spec sheet](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)