

Eaton SP6485D

Catalog Number: SP6485D

Eaton Crouse-Hinds series SP plug, 60A, 0.875-1.375" cable diameter, Three-wire, four-pole, Brass contacts, 60-400 Hz, Style 2, Copper-free aluminum, With cable grip and neoprene bushing, 480 Vac, Used with SRD threaded cap receptacles

General specifications



Product Name

Eaton Crouse-Hinds series SP plug

UPC

782274083124

Catalog Number

SP6485D

Product Weight

5.6 lb

Photo is representative

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 2

Class I, Division 1

Class II, Division 2

Class III

Class II, Division 1

NEMA Rating

7

12

3

9

Product specifications

Amperage Rating

60A

Configuration

Three-wire, four-pole

Cable diameter

0.875-1.375 in

Grounding style

Style 2

Voltage rating

480 Vac

Frequency rating

60-400 Hz

Material

Copper-free aluminum

Contact material

Brass

Special features

With cable grip and neoprene bushing

Type

Used with SRD threaded cap receptacles

Resources

Catalogs

[BHR and SRD Explosionproof Interlock Receptacles catalog page](#)

Certification reports

[BHR and SRD Explosionproof Interlock Receptacles UL certification](#)

[BHR and SRD Explosionproof Interlock Receptacles Canadian certification](#)

Installation instructions

[IF 308 - SRD Interlock Receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - SP6485D](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)