

# Eaton SP6567 NW

Catalog Number: SP6567 NW

Eaton Crouse-Hinds series SP plug, 60A, 1.375-1.875" cable diameter, Four-wire, five-pole, Brass contacts, 60-400 Hz, Style 2, Copper-free aluminum, With cable grip and neoprene bushing, 480 Vac, Used with SRD spring door receptacles

## General specifications



### Product Name

Eaton Crouse-Hinds series SP plug

### UPC

782274083148

### Catalog Number

SP6567 NW

### Product Weight

5.79 lb

Photo is representative

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class II, Division 1

Class I, Division 2

Class III

Class II, Division 2

Class I, Division 1

### NEMA Rating

12

7

9

3

## Product specifications

### Amperage Rating

60A

### Configuration

Four-wire, five-pole

### Cable diameter

1.375-1.875 in

### Grounding style

Style 2

### Voltage rating

480 Vac

### Frequency rating

60-400 Hz

### Material

Copper-free aluminum

### Contact material

Brass

### Special features

With cable grip and neoprene bushing

### Type

Used with SRD spring door receptacles

## Resources

### Catalogs

[BHR and SRD Explosionproof Interlock Receptacles catalog page](#)

### Certification reports

[BHR and SRD Explosionproof Interlock Receptacles UL certification](#)

[BHR and SRD Explosionproof Interlock Receptacles Canadian certification](#)

### Installation instructions

[IF 308 - SRD Interlock Receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - SP6567 NW](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)