

Eaton SRD6524 NW

Catalog Number: SRD6524 NW

Eaton Crouse-Hinds series SRD interlocked receptacle with switch, 60A, Through feed, Four-wire, five-pole, Brass contacts, Style 2, Copper-free aluminum, Spring door, 1-1/4", 480 Vac



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series SRD interlocked receptacle with switch	SRD6524 NW
	UPC
	782274083278
Product Length/Depth	Product Height
7.25 in	18.5 in
Product Width	Product Weight
9.94 in	21.18 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

7

9

12

Product specifications

Enclosure type

With switch

Amperage Rating

60A

Configuration

Four-wire, five-pole

Trade size

1-1/4"

Receptacle style

Spring door

Back box style

Through feed

Grounding style

Style 2

Voltage rating

480 Vac

Material

Copper-free aluminum

Contact material

Brass

Resources

Catalogs

[BHR and SRD Explosionproof Interlock Receptacles catalog page](#)

Certification reports

[BHR and SRD Explosionproof Interlock Receptacles Canadian certification](#)

[BHR and SRD Explosionproof Interlock Receptacles UL certification](#)

Installation instructions

[IF 308 - SRD Interlock Receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - SRD6524 NW](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)