

Eaton STN224-11{2}ZN

Catalog Number: STN224-11/2ZN

Eaton B-Line series Twirl-Nut stud nut, 0.8250" H x 1.5" L x 1.6250" W, Steel, Electro-plated, 3/8"-16 bolt size, 450 lbs load rating




Photo is representative

General specifications

Product Name	Catalog Number
Eaton B-Line series Twirl-Nut stud nut	STN224-11/2ZN
UPC	Product Length/Depth
781011414726	1.5 in
Product Height	Product Width
0.825 in	1.625 in
Product Weight	Certifications
0.084 lb	Not Applicable

Model

Bolt/thread/rod size

3/8"-16

Type

Stud twirl-nut

Load rating/capacity

Load rating (pull out strength)

450 lbs

Material/finish

Finish

Electro-plated

Material

Steel

Resources

Catalogs

[B-Line Safety Gratings Full Catalog](#)

[B-Line Series Strut Systems Catalog](#)

[Channel Nuts and Hardware Catalog Section](#)

Specifications and datasheets

[Eaton Specification Sheet - STN224-11/2ZN](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)