

Eaton STS361FW64

Catalog Number: STS361FW64

Eaton shunt trip safety switch, 30 A, Three-pole, 600 Vac, 250 Vdc, Alarm switch, Auxiliary- contact, 24 Vdc, 1 NO 1 NC, NEMA 4X, 304 stainless steel, Fusible, 600 V



Photo is representative

General specifications

Product Name

Eaton shunt trip safety switch

Catalog Number

STS361FW64

UPC

786685824819

Product Length/Depth

11.43 in

Product Height

21.58 in

Product Width

11.58 in

Product Weight

29 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

cUL Certified

Physical Attributes

Auxiliary contacts

Auxiliary contact

Enclosure

NEMA 4X

Enclosure material

304 stainless steel

Number Of Poles

Three-pole

Type

Shunt trip safety switch

Performance Ratings

Amperage Rating

30A

Coil voltage

24 Vdc

Protection

Fusible

Voltage rating

600 Vac, 250 Vdc

Miscellaneous

Contact configuration

1 NO 1 NC

Resources

Brochures

[Shunt trip safety switch Product Aid](#)

Multimedia

[ARMS Enclosed Circuit Breaker](#)

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

Specifications and datasheets

[Shunt trip safety switch Data Sheet](#)

[Eaton Specification Sheet - STS361FW64](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia