

Eaton STS361UW6

Catalog Number: STS361UW6

Eaton shunt trip safety switch, 30 A, Three-pole, 600 Vac, 250 Vdc, 24 Vdc, NEMA 4X, 304 stainless steel, Non-Fusible, 600 V



Photo is representative

General specifications

Product Name	Catalog Number
Eaton shunt trip safety switch	STS361UW6
UPC	Product Length/Depth
786685825335	11.43 in
Product Height	Product Width
21.58 in	11.58 in
Product Weight	Warranty
28 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed
cUL Certified

Physical Attributes

Enclosure

NEMA 4X

Enclosure material

304 stainless steel

Number Of Poles

Three-pole

Type

Shunt trip safety switch

Performance Ratings

Amperage Rating

30A

Coil voltage

24 Vdc

Protection

Non-Fusible

Voltage rating

600 Vac, 250 Vdc

Resources

Brochures

[Shunt trip safety switch Product Aid](#)

Multimedia

[Double Up on Safety](#)

[ARMS Enclosed Circuit Breaker](#)

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - STS361UW6](#)

[Shunt trip safety switch Data Sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)