

Eaton STS364FP61

Catalog Number: STS364FP61

Eaton shunt trip safety switch, 200 A, Three-pole, 600 Vac, 250 Vdc, Alarm switch, 24 Vdc, 1 NO-1 NC, NEMA 4, Painted steel, Fusible, 600 V



General specifications

Product Name

Eaton shunt trip safety switch

Catalog Number

STS364FP61

UPC

786685827179

Product Length/Depth

11.61 in

Product Height

35.38 in

Product Width

20.11 in

Product Weight

65 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

cUL Certified

Physical Attributes

Auxiliary contacts

Alarm switch

Enclosure

NEMA 4

Enclosure material

Painted steel

Number Of Poles

Three-pole

Type

Shunt trip safety switch

Performance Ratings

Amperage Rating

200A

Coil voltage

24 Vdc

Protection

Fusible

Voltage rating

600 Vac, 250 Vdc

Miscellaneous

Contact configuration

1 NO-1 NC

Resources

Brochures

[Shunt trip safety switch Product Aid](#)

Multimedia

[ARMS Enclosed Circuit Breaker](#)

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

Specifications and datasheets

[Shunt trip safety switch Data Sheet](#)

[Eaton Specification Sheet - STS364FP61](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia