

Eaton STS364ND34

Catalog Number: STS364ND34

Eaton shunt trip safety switch, 200 A, Three-pole, 600 Vac, 250 Vdc, 600 V, Alarm switch, 120 Vac, 1 NO 1 NC, NEMA 12, NEMA 3R, Fusible



General specifications

Product Name

Eaton shunt trip safety switch

Catalog Number

STS364ND34

UPC

786685827346

Product Length/Depth

11.61 in

Product Height

35.38 in

Product Width

20.11 in

Product Weight

67 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

cUL Certified



Powering Business Worldwide

Physical Attributes

Auxiliary contacts

Alarm switch

Enclosure

NEMA 12, NEMA 3R

Number Of Poles

Three-pole

Type

Shunt trip safety switch

Performance Ratings

Amperage Rating

200A

Coil voltage

120 Vac

Protection

Fusible

Voltage rating

600 Vac, 250 Vdc

Miscellaneous

Contact configuration

1 NO 1 NC

Resources

Brochures

[Shunt trip safety switch Product Aid](#)

Multimedia

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

[ARMS Enclosed Circuit Breaker](#)

Specifications and datasheets

[Shunt trip safety switch Data Sheet](#)

[Eaton Specification Sheet - STS364ND34](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)