

Eaton STS364NW64

Catalog Number: STS364NW64

Eaton shunt trip safety switch, 200 A, Three pole, 600 Vac, 250 Vdc, Alarm switch, 24 Vdc, 1 NO 1 NC, NEMA 4X, 304 stainless steel, Fusible, 600 V

General specifications



Product Name

Eaton shunt trip safety switch

Catalog Number

STS364NW64

UPC

786685827551

Product Length/Depth

11.61 in

Product Height

35.38 in

Product Width

20.11 in

Product Weight

67 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

cUL Certified

UL Listed

Physical Attributes

Auxiliary contacts

Alarm switch

Enclosure

NEMA 4X

Enclosure material

304 stainless steel

Number Of Poles

Three-pole

Type

Shunt trip safety switch

Performance Ratings

Amperage Rating

200A

Coil voltage

24 Vdc

Protection

Fusible

Voltage rating

600 Vac, 250 Vdc

Miscellaneous

Contact configuration

1 NO 1 NC

Resources

Brochures

[Shunt trip safety switch Product Aid](#)

Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

[ARMS Enclosed Circuit Breaker](#)

Specifications and datasheets

[Eaton Specification Sheet - STS364NW64](#)

[Shunt trip safety switch Data Sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia