

Eaton STS365FD6

Catalog Number: STS365FD6

Eaton shunt trip safety switch, 400 A, Three-pole, 600 Vac, 250 Vdc, 24 Vdc, NEMA 12, NEMA 3R, Fusible, 600 V



General specifications

Product Name	Catalog Number
Eaton shunt trip safety switch	STS365FD6
UPC	Product Length/Depth
786685827896	12.43 in
Product Height	Product Width
57.47 in	27.29 in
Product Weight	Warranty
130 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

cUL Certified
UL Listed

Physical Attributes

Enclosure

NEMA 12, NEMA 3R

Number Of Poles

Three-pole

Type

Shunt trip safety switch

Performance Ratings

Amperage Rating

400A

Coil voltage

24 Vdc

Protection

Fusible

Voltage rating

600 Vac, 250 Vdc

Resources

Brochures

[Shunt trip safety switch Product Aid](#)

Multimedia

[Switching Devices Flex Center](#)

[ARMS Enclosed Circuit Breaker](#)

[Double Up on Safety](#)

Specifications and datasheets

[Eaton Specification Sheet - STS365FD6](#)

[Shunt trip safety switch Data Sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)