

Eaton STS365FP61

Catalog Number: STS365FP61

Eaton shunt trip safety switch, 400 A, Three-pole, 600 Vac, 250 Vdc, Alarm switch, 24 Vdc, 1 NO-1 NC, NEMA 4, Painted steel, Fusible, 600 V



General specifications

Product Name

Eaton shunt trip safety switch

Catalog Number

STS365FP61

UPC

786685827995

Product Length/Depth

12.43 in

Product Height

57.47 in

Product Width

27.29 in

Product Weight

130 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

cUL Certified



Powering Business Worldwide

Physical Attributes

Auxiliary contacts

Alarm switch

Enclosure

NEMA 4

Enclosure material

Painted steel

Number Of Poles

Three-pole

Type

Shunt trip safety switch

Performance Ratings

Amperage Rating

400A

Coil voltage

24 Vdc

Protection

Fusible

Voltage rating

600 Vac, 250 Vdc

Miscellaneous

Contact configuration

1 NO-1 NC

Resources

Brochures

[Shunt trip safety switch Product Aid](#)

Multimedia

[ARMS Enclosed Circuit Breaker](#)

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - STS365FP61](#)

[Shunt trip safety switch Data Sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia