

# Eaton STS365UP6

Catalog Number: STS365UP6

Eaton shunt trip safety switch, 400 A, Three-pole, 600 Vac, 250 Vdc, 24 Vdc, NEMA 4, Painted steel, Non-Fusible, 600 V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton shunt trip safety switch	STS365UP6
<b>UPC</b>	<b>Product Length/Depth</b>
786685828534	12.43 in
<b>Product Height</b>	<b>Product Width</b>
57.47 in	27.29 in
<b>Product Weight</b>	<b>Warranty</b>
124 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

## Certifications

UL Listed  
cUL Certified

## Physical Attributes

### Enclosure

NEMA 4

### Enclosure material

Painted steel

### Number Of Poles

Three-pole

### Type

Shunt trip safety switch

## Performance Ratings

### Amperage Rating

400A

### Coil voltage

24 Vdc

### Protection

Non-Fusible

### Voltage rating

600 Vac, 250 Vdc

## Resources

### Brochures

[Shunt trip safety switch Product Aid](#)

### Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

[ARMS Enclosed Circuit Breaker](#)

### Specifications and datasheets

[Shunt trip safety switch Data Sheet](#)

[Eaton Specification Sheet - STS365UP6](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)