

Eaton STS367FP6

Catalog Number: STS367FP6

Eaton shunt trip safety switch, 800 A, Three pole, 600 Vac, 250 Vdc, 24 Vdc, NEMA 4, Painted steel, Fusible, 600 V



General specifications

Product Name	Catalog Number
Eaton shunt trip safety switch	STS367FP6
UPC	Product Length/Depth
786685829623	12.43 in
Product Height	Product Width
71.72 in	29.54 in
Product Weight	Warranty
167 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed
cUL Certified

Physical Attributes

Enclosure

NEMA 4

Enclosure material

Painted steel

Number Of Poles

Three-pole

Type

Shunt trip safety switch

Performance Ratings

Amperage Rating

800A

Coil voltage

24 Vdc

Protection

Fusible

Voltage rating

600 Vac, 250 Vdc

Resources

Brochures

[Shunt trip safety switch Product Aid](#)

Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

[ARMS Enclosed Circuit Breaker](#)

Specifications and datasheets

[Shunt trip safety switch Data Sheet](#)

[Eaton Specification Sheet - STS367FP6](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)