

Eaton STS367FW6

Catalog Number: STS367FW6

Eaton shunt trip safety switch, 800 A, Three pole, 600 Vac, 250 Vdc, 24 Vdc, NEMA 4X, 304 stainless steel, Fusible, 600 V

General specifications



Product Name

Eaton shunt trip safety switch

UPC

786685829715

Product Height

71.72 in

Product Weight

167 lb

Certifications

UL Listed

cUL Certified

Catalog Number

STS367FW6

Product Length/Depth

12.43 in

Product Width

29.54 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Physical Attributes

Enclosure

NEMA 4X

Enclosure material

304 stainless steel

Number Of Poles

Three-pole

Type

Shunt trip safety switch

Performance Ratings

Amperage Rating

800A

Coil voltage

24 Vdc

Protection

Fusible

Voltage rating

600 Vac, 250 Vdc

Resources

Brochures

[Shunt trip safety switch Product Aid](#)

Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

[ARMS Enclosed Circuit Breaker](#)

Specifications and datasheets

[Eaton Specification Sheet - STS367FW6](#)

[Shunt trip safety switch Data Sheet](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)