

Eaton STS367ND32

Catalog Number: STS367ND32

Eaton shunt trip safety switch, 800 A, Three-pole, 600 Vac, 250 Vdc, Auxiliary contact, 120 Vac, 1 NO 1 NC, NEMA 12, NEMA 3R, Fusible, 600 V



General specifications

Product Name

Eaton shunt trip safety switch

Catalog Number

STS367ND32

UPC

786685829791

Product Length/Depth

12.43 in

Product Height

71.72 in

Product Width

29.54 in

Product Weight

170 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

cUL Certified

UL Listed

Physical Attributes

Auxiliary contacts

Auxiliary contact

Enclosure

NEMA 12, NEMA 3R

Number Of Poles

Three-pole

Type

Shunt trip safety switch

Performance Ratings

Amperage Rating

800A

Coil voltage

120 Vac

Protection

Fusible

Voltage rating

600 Vac, 250 Vdc

Miscellaneous

Contact configuration

1 NO 1 NC

Resources

Brochures

[Shunt trip safety switch Product Aid](#)

Multimedia

[Switching Devices Flex Center](#)

[ARMS Enclosed Circuit Breaker](#)

[Double Up on Safety](#)

Specifications and datasheets

[Eaton Specification Sheet - STS367ND32](#)

[Shunt trip safety switch Data Sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)