

Eaton STS367NW6

Catalog Number: STS367NW6

Eaton shunt trip safety switch, 800 A, Three-pole, 600 Vac, 250 Vdc, 24 Vdc, NEMA 4X, 304 stainless steel, Fusible, 600 V

General specifications



Product Name

Eaton shunt trip safety switch

Catalog Number

STS367NW6

UPC

786685829999

Product Length/Depth

12.43 in

Product Height

71.72 in

Product Width

29.54 in

Product Weight

170 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

cUL Certified

Physical Attributes

Enclosure

NEMA 4X

Enclosure material

304 stainless steel

Number Of Poles

Three-pole

Type

Shunt trip safety switch

Performance Ratings

Amperage Rating

800A

Coil voltage

24 Vdc

Protection

Fusible

Voltage rating

600 Vac, 250 Vdc

Resources

Brochures

[Shunt trip safety switch Product Aid](#)

Multimedia

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

[ARMS Enclosed Circuit Breaker](#)

Specifications and datasheets

[Eaton Specification Sheet - STS367NW6](#)

[Shunt trip safety switch Data Sheet](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)