

# Eaton STS367UP34

Catalog Number: STS367UP34

Eaton shunt trip safety switch, 800 A, Three-pole, 600 Vac, 250 Vdc, Alarm switch, Auxiliary contact, 120 Vac, 1 NO 1 NC, NEMA 4, Painted steel, Non-Fusible, 600 V



## General specifications

### Product Name

Eaton shunt trip safety switch

### Catalog Number

STS367UP34

### UPC

786685830162

### Product Length/Depth

12.43 in

### Product Height

71.72 in

### Product Width

29.54 in

### Product Weight

158 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

cUL Certified

## Physical Attributes

### Auxiliary contacts

Auxiliary contact

### Enclosure

NEMA 4

### Enclosure material

Painted steel

### Number Of Poles

Three-pole

### Type

Shunt trip safety switch

## Performance Ratings

### Amperage Rating

800A

### Coil voltage

120 Vac

### Protection

Non-Fusible

### Voltage rating

600 Vac, 250 Vdc

## Miscellaneous

### Contact configuration

1 NO 1 NC

## Resources

### Brochures

[Shunt trip safety switch Product Aid](#)

### Multimedia

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

[ARMS Enclosed Circuit Breaker](#)

### Specifications and datasheets

[Eaton Specification Sheet - STS367UP34](#)

[Shunt trip safety switch Data Sheet](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)